



Benefits

- Adhesive complies with FDA 175.105 for indirect food contact

Features

- 2.6 mil white polypropylene offers excellent resistance to shrinkage, high temperatures, moisture, humidity and product contents
- High-performance, permanent acrylic adhesive adheres to a wide range of container types including low-surface energy HDPE
- Backed with a Flexcon® TracRite™ 92 polyester release liner for excellent on-press performance for tight-registration graphics
- Release liner provides a good diecutting base and allows for high-speed dispensing

Additional Details

Technical Data

Physical Properties

Thickness (Mils [microns])	Mils	Microns
Total Product	4.47	
Film	2.6 +/- 10 %	66
Adhesive	0.5-0.6 +/- 0.1 (3)	13 - 15
Liner	1.2 +/- 10 %	30

Test Method: ASTM D 3652 (Modified for use with non-tape product)

Adhesion Properties

Ultimate Peel from	Average Oz/In	(N/m)
Stainless Steel	44	484
Acrylic	45	495
Glass	50	550
Polypropylene	27	297

Test Method: ASTM D 903 (Modified for 72 hr. dwell time)

Additional Properties	Value	Test Method
Expected Shear (hours)	5	ASTM D 3654 Method A (1 hr. dwell, 1 sq. in, 4 lb. load)
Tack (g)	710	ASTM D 2979
Expected Exterior Life	Indoor use only	
Additional Information		
Service Temperature	-40°F to 212°F (-40°C to 100°C)	
Minimum Application Temperature	35°F (1.7°C)	
Storage Stability	Two years stored at 70°F (21°C) and 50% RH	

Product Performance and Suitability

Descriptive information, performance data, and recommendations for Flexcon products are guides and not specifications. Providing this information is to assist you and does not constitute a warranty of any kind by Flexcon.

Purchasers must independently determine the material's suitability for their intended use. No distributor, salesman, or representative of Flexcon is authorized to provide any warranty or guarantee beyond what is stated. FLEXCON MAKES NO WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING, BUT NOT LIMITED TO ANY IMPLIED WARRANTY OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, COURSE OF PERFORMANCE, OR TRADE USAGE.